


Pushbutton Units and Indicator Lights

Class 51, Hazardous Location NEMA Type 7 & 9 Devices

Selector switch operators

Selection and ordering data



Version	Key removal position	Lock number	Cam Code ^{1) 2)}	Short bushing Order No.	List Price \$ 1 unit	Long bushing Order No.	List Price \$ 1 unit	Pack Unit
Key-operated selector switches with 2 switching positions	Both	550CH	A	51SA6AE	233.00	51SA6AELB	233.00	1
	Left	550CH	A	51SA6AF	233.00	51SA6AFLB	233.00	
Maintained operation								
Spring return from right operation	Left	550CH	A	51SA6AC	248.00	51SA6ACLB	248.00	1
Key-operated selector switches with 3 switching positions	All	550CH	B	51SA6BE	233.00	51SA6BELB	233.00	1
			C	51SA6CE	233.00	51SA6CELB	233.00	
Maintained operation								
	Left	550CH	D	51SA6DE	233.00	51SA6DELB	233.00	1
			E	51SA6EE	233.00	51SA6EELB	233.00	
			G	51SA6GE	233.00	51SA6GELB	233.00	
			B	51SA6BF	233.00	51SA6BFLB	233.00	
	Right	550CH	C	51SA6CF	233.00	51SA6CFLB	233.00	1
			D	51SA6DF	233.00	51SA6DFLB	233.00	
			E	51SA6EF	233.00	51SA6EFLB	233.00	
			G	51SA6GF	233.00	51SA6GFLB	233.00	
	Center	550CH	B	51SA6BG	233.00	51SA6BGLB	233.00	1
			C	51SA6CG	233.00	51SA6CGLB	233.00	
			D	51SA6DG	233.00	51SA6DGLB	233.00	
			E	51SA6EG	233.00	51SA6EGLB	233.00	
	Left and Center	550CH	G	51SA6GG	233.00	51SA6GGLB	233.00	1
			B	51SA6BH	233.00	51SA6BHLB	233.00	
			C	51SA6CH	233.00	51SA6CHLB	233.00	
			D	51SA6DH	233.00	51SA6DHLB	233.00	
	Center	550CH	E	51SA6EH	233.00	51SA6EHLB	233.00	1
			G	51SA6GH	233.00	51SA6GHLB	233.00	
			B	51SA6BK	233.00	51SA6BKLb	233.00	
			C	51SA6CK	233.00	51SA6CKLB	233.00	
	Left and Center	550CH	D	51SA6DK	233.00	51SA6DKLB	233.00	1
			E	51SA6EK	233.00	51SA6EKLB	233.00	
			G	51SA6GK	233.00	51SA6GKLB	233.00	
			B	51SA6BU	248.00	51SA6BULB	248.00	
Spring return from right operation	Center	550CH	C	51SA6CU	248.00	51SA6CULB	248.00	1
			D	51SA6DU	248.00	51SA6DULB	248.00	
			E	51SA6EU	248.00	51SA6EULB	248.00	
			G	51SA6GU	248.00	51SA6GULB	248.00	
Spring return from left operation	Center	550CH	B	51SA6BT	248.00	51SA6BTLB	248.00	1
			C	51SA6CT	248.00	51SA6CTLB	248.00	
			D	51SA6DT	248.00	51SA6DTLB	248.00	
			E	51SA6ET	248.00	51SA6ETLB	248.00	
	Center	550CH	G	51SA6GT	248.00	51SA6GTLB	248.00	1
			B	51SA6BV	248.00	51SA6BVLB	248.00	
			C	51SA6CV	248.00	51SA6CVLB	248.00	
			D	51SA6DV	248.00	51SA6DVLB	248.00	
Spring return from left and right operation	Center	550CH	E	51SA6EV	248.00	51SA6EVLB	248.00	1
			G	51SA6GV	248.00	51SA6GVLB	248.00	

Lock types keyed different from standard - up to 25 per order

5

5

To order special locks for keyed selector switches, append corresponding 'X' suffix to part number

Ordering example:
51SA6AEX298

#549CH	X639	1
#548CH	X640	1
#547CH	X641	1
#501CH	X642	1
#506CH	X643	1

1) C cam limited to 4 single or double pole blocks on spring return operators.

2) For contact operation, see cam selection chart on page 10/127.