

Definite Purpose Controls

D.P. Cross Reference

Poles	Amps	Volts	SIEMENS	Cutler Hammer	Arrow Hart	ABB	Allen Bradley	Joslyn Clark	Fasco	General Electric	Square D	Steveco	Products Unlimited (OEM)
1	25	24	45DG10AJA	C25CNB125T	C251NU10	-	400-DP25NJ1	A77-306654A-3	1S25-A	CR453CB3HAA	8910DP21V14	94385	3100-15Q1
-	25	120	45DG10AFA	C25CNB125A	C251NU20	-	400-DP25ND1	A77306654A-1	1S25-B	CR453CB3AAA	8910DP21V02	94386	3100-15T1
-	25	208/240	45DG10AGA	C25CNB125B	C251NU30	-	400-DP25NA1	A77-306654A-2	1S25-C	CR453CB3BAA	8910DP21V09	94387	3100-15U1
1	30	24	45EG10AJA	C25CNB130T	C301NU10	DP30C1P-F	400-DP30NJ1	A77-306653A-3	1S30-A	CR453CC3HAA	8910DP31V14	94388	3100-15Q2
-	30	120	45EG10AFA	C25CNB130A	C301NU20	DP30C1P-1	400-DP30ND1	A77-306653A-1	1S30-B	CR453CC3AAA	8910DP31V02	94389	3100-15T2
-	30	208/240	45EG10AGA	C25CNB130B	C301NU30	DP30C1P-2	400-DP30NA1	A77-3066531-2	1S30-C	CR453CC3BAA	8910DP31V09	94390	3100-15U2
1	40	24	45GG10AJA	C25CNB140T	-	-	-	-	-	-	8910DP41V14	-	3100-15Q19
-	40	120	45GG10AFA	C25CNB140A	-	-	-	-	-	-	8910DP41V02	-	3100-15T19
-	40	208/240	45GG10AGA	C25CNB140B	-	-	-	-	-	-	8910DP41V09	-	3100-15U19
2	20	24	45CG20AJ	C25BNB220T	C202U10	-	-	A77-306680A-3	2S20-A	CR453CA2HAA	8910DP12V14	90234	3100-20Q3
-	20	120	45CG20AF	C25BNB220A	C202U20	-	-	A77-306680A-1	2S20-B	CR453CA2AAA	8910DP12V02	90235	3100-20T3
-	20	208/240	45CG20AG	C25BNB220B	C202U30	-	-	A77-306680A-2	2S20-C	CR453CA2BAA	8910DP12V09	90236	3100-20U3
-	20	277	45CG20AL	C25BNB220H	-	-	-	-	-	CR453CA2FAA	8910DP12V04	-	3100-20V3
2	30	24	45EG20AJ	C25BNB230T	C302U10	-	400-DP30NJ2	A77-306657A-3	2S30-A	CR453CC2HAA	8910DPA32V14	90244	3100-20Q6
-	30	120	45EG20AF	C25BNB230A	C302U20	-	400-DP30ND2	A77-306657A-1	2S30-B	CR453CC2AAA	8910DPA32V02	90245	3100-20T6
-	30	208/240	45EG20AG	C25BNB230B	C302U30	-	400-DP30NA2	A77-306657A-2	2S30-C	CR453CC2BAA	8910DPA32V09	90246	3100-20U6
-	30	277	45EG20AL	C25BNB230H	C302050	-	400-DP30NF2	-	-	CR453CC2FAA	8910DPA32V04	-	3100-20V6
2	40	24	45GG20AJ	C25BNB240T	CA01NU10	-	-	-	-	CR453CE2HBB	8910DP42V14	-	3100-20Q18
-	40	120	45GG20AF	C25BNB240A	CA01NU20	-	-	-	-	CR453CE2ABB	8910DP42V02	-	3100-20T18
-	40	208/240	45GG20AG	C25BNB240B	CA01NU30	-	-	-	-	CR453CE2BBB	8910DP42V09	-	3100-20U18
3	25	24	42AF35AJ	C25DND325T	ACC230UM10	-	400-DP25NJ3	-	3M25-A	CR453AB3HAA	8910DPA23V14	90160	3100-30Q8
-	25	120	42AF35AF	C25DND325A	ACC230UM20	-	400-DP25ND3	-	3M25-B	CR453AB3AAA	8910DPA23V02	90161	3100-30T8
-	25	208/240	42AF35AG	C25DND325B	ACC230UM30	-	400-DP25NA3	-	3M25-C	CR453AB3BAA	8910DPA23V09	90162	3100-30U8
3	30	24	42BF35AJ	C25DND330T	ACC330UM10	DP30C3P-F	400-DP30NJ3	A77-309044A-3	3M30-A	CR453AC3HAA	8910DPA33V14	90163	3100-30Q9
-	30	120	42BF35AF	C25DND330A	ACC330UM20	DP30C3P-1	400-DP30ND3	A77-309044A-1	3M30-B	CR453AC3AAA	8910DPA33V02	90164	3100-30T99
-	30	208/240	42BF35AG	C25DND330B	ACC330UM30	DP30C3P-2	400-DP30NA3	A77-309044A-2	3M30-C	CR453AC3BAA	8910DPA33V03	90165	3100-30U9
3	40	24	42CF35AJ	C25DNF340T	ACC430UM10	DP40C4P-F	400-DP40NJ3	A77-309046A-3	3M40-A	CR453AD3HBB	8910DPA43V14	90170	3100-30Q10
-	40	120	42CF35AF	C25DNF340A	ACC430UM20	DP40C4P-1	400-DP40ND3	A77-309046A-1	3M40-B	CR453AD3ABB	8910DPA43V02	90171	3100-30T10
-	40	208/240	42CF35AG	C25DNF340B	ACC430UM30	DP40C4P-2	400-DP40NA3	A77-309046A-2	3M40-C	CR453AD3BBB	8910DPA43V09	90172	3100-30U10
3	50	24	42DF35AJ	C25FNF350T	ACC530U10	-	400-DP50NJ3	A77-288514A-3	3L50-A	CR353FE3BH1	8910DPA53V14	92459	3100-30Q16
-	50	120	42DF35AF	C25FNF350A	ACC530U20	-	400-DP50ND3	A77-288514A-1	3L50-B	CR353FE3BA1	8910DPA53V02	92460	3100-30T16
-	50	208/240	42DF35AG	C25FNF350B	ACC530U30	-	400-DP50NA3	A77-288514A-2	3L50-C	CR353FE3BB1	8910DPA53V09	92461	3100-30U16
3	60	24	42EF35AJ	C25FNF360T	ACC630U10	DP60C3P-F	400-DP60NJ3	A77-288517A-3	3L60-A	CR353FF3BH1	8910DPA63V14	92462	3100-30Q17
-	60	120	42EF35AF	C25FNF360A	ACC630U20	DP60C3P-1	400-DP60ND3	A77-288517A-1	3L60-B	CR353FF3BA1	8910DPA63V02	92463	3100-30T17
-	60	208/240	42EF35AG	C25FNF360B	ACC630U30	DP60C3P-2	400-DP60NA3	A77-288517A-2	3L60-C	CR353FF3BB1	8910DPA63V09	92464	3100-30U17
3	75	24	42FE35AJ106	C25FNF375T	ACC730U10	-	400-DP75NJ3	A77-288520A-3	-	CR353EG3BH1	8910DPA73V14	92465	3186-30I75
-	75	120	42FE35AF106	C25FNF375A	ACC730U20	-	400-DP75ND3	A77-288520A-1	-	CR353EG3BA1	8910DPA73V02	92467	3186-30J75
-	75	208/240	42FE35AG106	C25FNF375B	ACC730U30	-	400-DP75NA3	A77-288520A-2	-	CR353EG3BB1	8910DPA73V09	92468	3186-30K75
3	90	24	42GE35AJ106	C25GNF390T	-	-	-	-	-	CR353EH3BH1	8910DPA93V14	92469	3186-30I90
-	90	120	42GE35AF106	C25GNF390A	ACC930U20	-	-	-	-	CR353EH3BA1	8910DPA93V02	-	3186-30J90
-	90	208/240	42GE35AG106	C25GNF390B	ACC930U30	-	-	-	-	CR353EH3BB1	8910DPA93V09	-	3186-30K90
3	120	24	42HF35AJ	C25HNF3120T	-	-	-	-	-	CR353GJ3AH1	8910DPA123V14	-	3100-30Q12
-	120	120	42HF35AF	C25HNF3120A	ACC1230U20	-	-	-	-	CR353GJ3AA1	8910DPA123V02	-	3100-30T12
-	120	208/240	42HF35AG	C25HNF3120B	ACC1230U30	-	-	-	-	CR353GJ3AB1	8910DPA123V09	-	3100-30U12
4	40	24	42CF25AJ	C25ENF440T	ACC440UM10	-	-	-	-	CR353AD4BH1	8910DPA44V14	-	3100-40Q10
-	40	120	42CF25AF	C25ENF440A	ACC440UM20	-	-	-	-	CR353AD4BA1	8910DPA44V02	-	3100-40T10
-	40	208/240	42CF25AG	C25ENF440B	ACC440UM30	-	-	-	-	CR353AD4BB1	8910DPA44V09	-	3100-40U10

This cross reference does not purport to cover all details or variations in equipment, nor to provide for every possible contingency to be met in connection with installation, operation, or maintenance. Should further information be desired or should particular problems arise which are not covered sufficiently for the purchaser's purposes, the matter should be referred to the local Siemens Energy & Automation Controls sales office.

The contents of this cross reference shall not become part or modify any prior or existing agreement, commitment or relationship. The sales contract contains the entire obligation of Siemens Energy & Automation, Inc. The warranty contained in the contract between the parties is the sole warranty of Siemens Energy & Automation, Inc. Any statements contained herein do not create new warranties or modify the existing warranty.