




• Revised •  
03/20/2012

# Pushbutton Units and Indicator Lights

## 30 mm, Black Max Corrosion Resistant, Class 52

Complete units

### Selection and ordering data

Version	Color of actuator	Contact blocks	Flush cap order no.①	Extended cap order no.①	List Price	Mushroom head order no.①	List Price	Pack	
					\$		\$	Unit	
Pushbutton unit with assembled contact blocks	black	1 NO	52PX8A1K	52PX8B1K		52PX9□1K		1	
	red	1 NO	52PX8A2K	52PX8B2K		52PX9□2K			
	green	1 NO	52PX8A3K	52PX8B3K		52PX9□3K			
	yellow	1 NO	52PX8A4K	52PX8B4K		52PX9□4K			
Flush assembled pushbutton		blue	1 NO	52PX8A5K	52PX8B5K		52PX9□5K	1	
		gray	1 NO	52PX8A6K	52PX8B6K		52PX9□6K		
		orange	1 NO	52PX8A8K	52PX8B8K		52PX9□8K		
		black	1 NC	52PX8A1J	52PX8B1J		52PX9□1J	1	
	red	1 NC	52PX8A2J	52PX8B2J		52PX9□2J			
	green	1 NC	52PX8A3J	52PX8B3J		52PX9□3J			
	yellow	1 NC	52PX8A4J	52PX8B4J		52PX9□4J			
	blue	1 NC	52PX8A5J	52PX8B5J		52PX9□5J	1		
	gray	1 NC	52PX8A6J	52PX8B6J		52PX9□6J			
	orange	1 NC	52PX8A8J	52PX8B8J		52PX9□8J			
	Extended assembled pushbutton		black	1 NO + 1 NC	52PX8A1A	52PX8B1A		52PX9□1A	1
			red	1 NO + 1 NC	52PX8A2A	52PX8B2A		52PX9□2A	
green			1 NO + 1 NC	52PX8A3A	52PX8B3A		52PX9□3A		
yellow			1 NO + 1 NC	52PX8A4A	52PX8B4A		52PX9□4A		
blue		1 NO + 1 NC	52PX8A5A	52PX8B5A		52PX9□5A	1		
gray		1 NO + 1 NC	52PX8A6A	52PX8B6A		52PX9□6A			
orange		1 NO + 1 NC	52PX8A8A	52PX8B8A		52PX9□8A			
black		2 NO	52PX8A1F	52PX8B1F		52PX9□1F	1		
red		2 NO	52PX8A2F	52PX8B2F		52PX9□2F			
green		2 NO	52PX8A3F	52PX8B3F		52PX9□3F			
yellow		2 NO	52PX8A4F	52PX8B4F		52PX9□4F			
blue		2 NO	52PX8A5F	52PX8B5F		52PX9□5F	1		
gray	2 NO	52PX8A6F	52PX8B6F		52PX9□6F				
orange	2 NO	52PX8A8F	52PX8B8F		52PX9□8F				
Mushroom head assembled pushbutton		black	2 NC	52PX8A1G	52PX8B1G		52PX9□1G	1	
		red	2 NC	52PX8A2G	52PX8B2G		52PX9□2G		
		green	2 NC	52PX8A3G	52PX8B3G		52PX9□3G		
		yellow	2 NC	52PX8A4G	52PX8B4G		52PX9□4G		
	blue	2 NC	52PX8A5G	52PX8B5G		52PX9□5G	1		
	gray	2 NC	52PX8A6G	52PX8B6G		52PX9□6G			
	orange	2 NC	52PX8A8G	52PX8B8G		52PX9□8G			
	black	2 NO + 2 NC	52PX8A1B	52PX8B1B		52PX9□1B	1		
	red	2 NO + 2 NC	52PX8A2B	52PX8B2B		52PX9□2B			
	green	2 NO + 2 NC	52PX8A3B	52PX8B3B		52PX9□3B			
	yellow	2 NO + 2 NC	52PX8A4B	52PX8B4B		52PX9□4B			
	blue	2 NO + 2 NC	52PX8A5B	52PX8B5B		52PX9□5B	1		
gray	2 NO + 2 NC	52PX8A6B	52PX8B6B		52PX9□6B				
orange	2 NO + 2 NC	52PX8A8B	52PX8B8B		52PX9□8B				

Order no. change  
Small operating head - 1<sup>5</sup>/<sub>8</sub>" (41.3 mm)  
Large operating head - 2.5" (63.5 mm)

D  
E

Technical Specifications  
on page 10/169A

① For other contact block assemblies, replace the 8th character of catalog number:  
C = 3 NO + 3 NC  
D = 4 NO + 4 NC  
E = 1 NC (Early Break)  
H = 1 no (Early Make)