

Circuit Breakers

Lug Data

Reference

Circuit Breaker Type	Circuit Breaker Ampere Rating	Cables Per Connector	Connector Wire Range
QP, QPH, HQP, Plug-in	LOAD SIDE		
	10	2	#16 AWG Cu
	15–20	1 1	#14–#8 AWG Cu #12–#8 AWG Al
	25–35	1 1	#14–#6 AWG Cu #14–#6 AWG Al
	40–50	1 1	#8–#6 AWG Cu #8–#4 AWG Al
	55–70	1 1	#8–#4 AWG Cu #8–#2 AWG Al
	80–100	1 1	#4–#1/0 AWG Cu #2–#1/0 AWG Al
	110–125 [®]	1 1	#2–#1/0 AWG Cu #1/0–#2/0 AWG Al
QT	15–35	1 1	#14–#8 AWG Cu #12–#8 AWG Al
	40	1	#8 AWG CU-AL
	40–50	1 1	#8–#6 AWG Cu #8–#4 AWG Al
QPF, QPHF	15–30	1 1	#14–#10 AWG Cu #12–#8 AWG Al
	40–60	1 1	#8–#6 AWG Cu #8–#4 AWG Al
QAF, QAFH	15–20	1 1	#14–#12 AWG Cu #12–#10 AWG Al
QD	15–20	2	#14–#8 AWG Cu Only
	15–20	1	#14–#12 AWG Cu #12–#10 AWG Al
	25–35	1 1	#10–#8 AWG Cu #10–#6 AWG Al
	40–60	1 1	#8–#6 AWG Cu #8–#4 AWG Al
QN, QNH, HQN	150–200	1	#1–300kcmil Cu-Al
EQ8681-Ultimate	100	1	#4–3/0 AWG Cu-Al
EQ8682-Ultimate	125	1	#4–3/0 AWG Cu-Al
EQ8693-Ultimate	150	1	#1–300kcmil Cu-Al
EQ8695-Ultimate	200	1	#1–300kcmil Cu-Al
EQ8696-Ultimate	225	1	#1–300kcmil Cu-Al
QPP, QPPH, HQPP, HQPPH	125	1 1	#1 AWG Cu #2/0 AWG Al
	150	1 1	#1/0 AWG Cu #3/0 AWG Al
	175	1 1	#2/0 AWG Cu #4/0 AWG Al
	200	1 1	#3/0 AWG Cu 250kcmil AWG Al
	225	1 1	#4/0 AWG Cu 300kcmil AWG Al
	EQ9675-EQIII	100	1 1
EQ9677-EQIII	125	1 1	#1 AWG Cu #2/0 AWG Al
EQ9683-EQIII	150	1 1	#1/0 AWG Cu #3/0 AWG Al
EQ9685-EQIII	200	1 1	#3/0 AWG Cu 250kcmil AWG Al
EQ9686-EQIII	225	1 1	#4/0 AWG Cu 300kcmil AWG Al
QPJ	125–200	1	#2–300kcmil Cu-Al

1
LOAD CENTERS &
CIRCUIT BREAKERS