

# AC Disconnects

## 1Ø, NEMA 3R Rated



WN2060



WN2060GFCI



WF2060PL



WNAS2060GFCI

### Steel AC Disconnects<sup>①②</sup>

Ampere Rating	Disconnect Type	Catalog Number	Horse Power Rating	Dimensions			List Price \$	Pallet Qty.①
				Height	Width	Depth		
30	Fused Pullout	WF2030	3	7¼	5	2½	154.00	360
60	Fused Pullout	WF2060	10	9	5	2½	154.00	360
60	Non-fused Pullout	WN2060	10	7¼	5	2½	154.00	360
60	Non-automatic Switch	WNAS2060	10	7¼	5	2½	184.00	360

### Plastic AC Disconnects<sup>①②</sup>

Ampere Rating	Disconnect Type	Catalog Number	Horse Power Rating	Dimensions			List Price \$	Pallet Qty.①
				Height	Width	Depth		
30	Fused Pullout	WF2030PL	3	7¼	5	2½	235.00	216
60	Fused Pullout	WF2060PL	10	7¼	5	2½	235.00	216
60	Non-fused Pullout	WN2060PL	10	7¼	5	2½	214.00	360
60	<b>NEW</b> Non-Fused Pullout	WN2060PLX	10	8	5¾	3½	224.00	288
60	<b>NEW</b> Non-automatic switch	WNAS2060PL	10	7¼	5	2½	360.00	360

### Steel AC Disconnects with 15 Amp GFCI Receptacle<sup>①②</sup>

Ampere Rating	Disconnect Type	Catalog Number	Horse Power Rating	Dimensions			List Price \$	Pallet Qty.①
				Height	Width	Depth		
30	Fused Pullout	WF2030GFCI	3	9	6⅞	5⅝	500.00	112
60	Fused Pullout	WF2060GFCI	10	9	6⅞	5⅝	500.00	112
60	Non-fused Pullout	WN2060GFCI	10	7⅞	5¾	5⅝	463.00	144
60	Non-automatic Switch	WNAS2060GFCI	10	7⅞	5¾	5⅝	500.00	144

### Wire Range Table

Connector	Copper		Aluminum	
	Solid	Stranded	Solid	Stranded
Line	#14-8	#14-3	#12-8	#12-3
Load	#14-8	#14-3	#12-8	#12-3
Neutral	#12-8	#12-2	#12-8	#12-2
Equip. Grnd	#12-8	#12-2	#12-8	#12-2

① Add a "BP" to the end of the catalog number to order in pallet quantities, example: WN2060BP.

② Accepts Class H Fuse