

# Circuit Breakers

## Lug Data

Circuit Breaker Type	Circuit Breaker Ampere Rating	Cables Per Connector	Connector Wire Range
<b>MP-T, MP-HT, MP-MT</b>	<b>LOAD SIDE</b>		
	7	2	#18-#14 CU
	10	2	#16-#14 CU
	15-20	1	#14-#8 AWG Cu #12-#8 AWG Al
	25-35	1	#14-#6 AWG Cu #14-#6 AWG Al
	40-50	1	#8-#6 AWG Cu #8-#4 AWG Al
	55-70	1	#8-#4 AWG Cu #8-#2 AWG Al
	80-100	1	#4-#1/0 AWG Cu #2-#1/0 AWG Al
	110-125 <sup>②</sup>	1	#2-#1/0 AWG Cu #1/0-#2/0 AWG Al
<b>MH-T</b>	15-35	1	#14-#8 AWG Cu #12-#8 AWG Al
	40	1	#8 AWG CU-AL
	40-50	1	#8-#6 AWG Cu #8-#4 AWG Al
<b>MP-GT, MP-HGT, MP-ET, MP-HET BLF, BLHF, BLE, BLEH</b>	15-30	1	#14-#10 AWG Cu #12-#8 AWG Al
	40-60	1	#8-#6 AWG Cu #8-#4 AWG Al
<b>MP-AT, MP-HAT, BAF, BAFH</b>	15-20	1	#14-#12 AWG Cu #12-#10 AWG Al
<b>MSQ</b>	15-20	2	#14-#8 AWG Cu Only
	15-20	1	#14-#12 AWG Cu #12-#10 AWG Al
	25-35	1	#10-#8 AWG Cu #10-#6 AWG Al
	40-60	1	#8-#6 AWG Cu #8-#4 AWG Al
<b>MD-T, MD-HT, MD-MT, MD-PT, MD-TR, MD-HTR, MD-MTR, MD-PTR</b>	150-200	1	#1-300kcmil Cu-Al
<b>M1</b>	100	1	#4-3/0 AWG Cu-Al
	125	1	#4-3/0 AWG Cu-Al
<b>M2</b>	150	1	#1-300kcmil Cu-Al
	200	1	#1-300kcmil Cu-Al
	225	1	#1-300kcmil Cu-Al
<b>MPP-T, MPP-HT, MPP-MT, MPP-PT</b>	125	1	#1 AWG Cu #2/0 AWG Al
	150	1	#1/0 AWG Cu #3/0 AWG Al
	175	1	#2/0 AWG Cu #4/0 AWG Al
	200	1	#3/0 AWG Cu 250kcmil AWG Al
	225	1	#4/0 AWG Cu 300kcmil AWG Al
		1	
<b>MQ, MQH, MQL</b>	60-225	1	#6-300kcmil Cu #4-300kcmil Al