

Meter Sockets

Ringless Type, Lever Bypass & No Bypass Types



RK48507



S48104-02



RK78061

320 Amp Continuous/400 Amp Max Meter Mounting Equipment Lever Bypass, 1 Phase, 3 Wire or 3 Phase, 3 Wire, 600V^{③⑤} Commercial/Industrial

(These units not rated for 3 Phase, 4 Wire Service)

| Catalog Number | Replaces | Dimensions (inches) | | | Cont. Amps | Service | Wire Range | No. of Jaws | Hub Opening | KO Fig. | List Price \$ |
|---------------------------|------------|---------------------|------|-----|------------|----------|-------------|-------------|--------------|---------|---------------|
| | | H | W | D | | | | | | | |
| 4 or 5 TERMINAL | | | | | | | | | | | |
| S48704-82GP ^{②④} | RK178A | 34.0 | 20.0 | 6.0 | 320 | OH/UG-SW | 3/8-24 Stud | 4 | HD CL. Plate | 11 | 719.94 |
| RK178C-LI ^② | — | 34.0 | 20.0 | 6.0 | 320 | OH/UG-SW | 3/8-24 Stud | 5 | HD CL. Plate | 11 | 672.02 |
| S47704-01NU ^① | RK173AH | 28.0 | 14.0 | 6.0 | 320 | OH/UG | 1/2-20 Stud | 4 | HD Opening | 13 | 647.52 |
| S47705-01NU ^② | RK173CH | 28.0 | 14.0 | 6.0 | 320 | OH/UG | 1/2-20 Stud | 5 | HD Opening | 13 | 773.19 |
| S48104-02 | RK178ARR | 31.0 | 16.0 | 5.1 | 320 | OH/UG-SW | 3/8-24 Stud | 4 | HD CL. Plate | 14 | 1016.01 |
| S9804-9144 ^① | RK173AHJNU | 22.0 | 16.0 | 6.0 | 320 | OH/UG | 3/8-24 Stud | 4 | HD Opening | 13 | 498.42 |
| S9804-9146 ^① | RK178AHJNU | 34.0 | 20.0 | 6.0 | 320 | OH/UG | 3/8-24 Stud | 4 | HD CL. Plate | 11 | 749.76 |

320 Amp Continuous 400 Amp Max Meter Mounting Equipment Lever Bypass, 3 Phase, 4 Wire, 600V, Commercial/Industrial^{③⑤}

| Catalog Number | Replaces | Dimensions (inches) | | | Cont. Amps | Service | Wire Range | No. of Jaws | Hub Opening | KO Fig. | List Price \$ |
|---------------------------|------------|---------------------|------|-----|------------|----------|-------------|-------------|--------------|---------|---------------|
| | | H | W | D | | | | | | | |
| 7 TERMINAL | | | | | | | | | | | |
| S48707-82GP ^{②④} | RK178G | 34.0 | 20.0 | 6.0 | 320 | OH/UG-SW | 3/8-24 Stud | 7 | HD CL. Plate | 11 | 870.11 |
| S47707-01NU ^① | RK173GH | 28.0 | 14.0 | 6.0 | 320 | OH/UG | 1/2-20 Stud | 7 | HD Opening | 13 | 773.19 |
| S9804-9145 ^① | RK173GHJNU | 22.0 | 16.0 | 6.0 | 320 | OH/UG | 3/8-24 Stud | 7 | HD Opening | 34 | 634.74 |
| S9804-9147 ^① | RK178GHJNU | 34.0 | 20.0 | 6.0 | 320 | OH/UG | 3/8-24 Stud | 7 | HD CL. Plate | 11 | 890.34 |

400 Amp Continuous 400 Amp Max Meter Mounting Equipment No Bypass, 1 Phase, 3 Wire, 300V, Commercial/Industrial^{①③④}

| Catalog Number | Replaces | Dimensions (inches) | | | Cont. Amps | Service | Wire Range | No. of Jaws | Hub Opening | KO Fig. | List Price \$ |
|--------------------------------------------------------|----------|---------------------|------|-----|------------|---------|------------|-------------|--------------|---------|---------------|
| | | H | W | D | | | | | | | |
| Landis & Gyr Type K4UT Bolt-on Meter Socket | | | | | | | | | | | |
| 4 TERMINAL | | | | | | | | | | | |
| RK48507 | — | 36.0 | 18.0 | 6.1 | 400 | OH/UG | (2) #4-500 | 4 | HD CL. Plate | 38 | 877.56 |

400 Amp Continuous 400 Amp Max Meter Mounting Equipment No Bypass, 3 Phase, 4 Wire, 600V, Commercial/Industrial^{③⑤⑥}

| Catalog Number | Replaces | Dimensions (inches) | | | Cont. Amps | Service | Wire Range | No. of Jaws | Hub Opening | KO Fig. | List Price \$ |
|------------------------------------------------------|----------|---------------------|------|-----|------------|---------|-------------|-------------|--------------|---------|---------------|
| | | H | W | D | | | | | | | |
| Landis & Gyr Type K7 Bolt-on Meter Socket | | | | | | | | | | | |
| RK78061 | — | 34.0 | 20.0 | 6.0 | 400 | UG | 1/2-20 Stud | 7 | HD CL. Plate | 15 | 1646.49 |

Contact utility or sales office for approval by your local utility prior to installation.

①7/16" Barrel lock knockout
 ②7/8" Barrel lock knockout
 ③Ground lug included
 ④Anti-inversion clip included

⑤Lugs not included, order separately
 ⑥Bolt-in meter socket