

# Meter Mains

## Meter Mains, 100A-400A

- UL listed
- Pad locking provisions on all devices
- Horn bypass and 5th jaw available as noted
- Side hinged door with one screw removal where shown
- Suitable for use only as service entrance equipment
- Contact local utility to confirm meter socket placement prior to installation
- See end of section for 5th jaw, main breaker, dimensions and wiring diagrams



Figure 1



**JC0202B1125RJB**  
meter mains, side hinge door

Figure 2



**JC0406L1200RHJB**  
200A meter main, 6 circuits

Figure 3



**JC0404L1400RLM**  
400A meter main, two field installed mains

Figure 4



**JC002CZ**  
125A meter main

Figure 5



**JC002CS**  
meter main, OH feed only

3  
METER CENTERS

Side-By-Side Construction Meter Mains												
Amps Max.	No. of Spaces	Max. Circuits	Cover Type	Mounting	Service	Bypass Type	Catalog Number	Dimensions <sup>①</sup>			List Price \$	Figure
								Height	Width	Depth		
125	2	2	Ring	Surface	OH	—	<b>JC002CZ</b> <sup>②</sup>	14.1	14.1	4.6	375.00	4
125	2	2	Ringless	Flush	OH/UG	Horn	<b>JC0202B1125RJB</b> <sup>③</sup>	17.0	16.0	5.0	1232.00	1
200	2	2	Ring	Surface	OH/UG	—	<b>JC0202B1200</b> <sup>③</sup>	17.0	16.0	5.0	1849.00	1
200	2	2	Ringless	Flush	OH/UG	—	<b>JC0202B1200R</b> <sup>③</sup>	17.0	16.0	5.0	1849.00	1
200	2	2	Ringless	Flush	OH/UG	Horn	<b>JC0202B1200RJB</b> <sup>③</sup>	17.0	16.0	5.0	1849.00	1
200	4	6	Ring	Flush	OH/UG	—	<b>JC0406L1200H</b> <sup>③</sup>	19.7	17.1	5.0	1005.00	2
200	4	6	Ringless	Surface	OH/UG	—	<b>JC0406L1200RH</b> <sup>③</sup>	19.7	17.1	5.0	1061.00	2
200	4	6	Ringless	Flush	OH/UG	Horn	<b>JC0406L1200RHJB</b> <sup>③</sup>	19.7	17.1	5.0	1097.00	2
400	2	2	Ringless	Surface	OH/UG	Lever	<b>JC0404L1400RLM</b> <sup>③</sup>	29.0	27.0	6.0	3083.00	3

Over-Under Construction Meter Mains												
Amps Max.	No. of Spaces	Max. Circuits	Cover Type	Mounting	Service	Bypass Type	Catalog Number	Dimensions <sup>①</sup>			List Price \$	Figure
								Height	Width	Depth		
100	2	2	Ring	Surface	OH	—	<b>JC002CS</b> <sup>②</sup>	18.1	7.0	3.6	368.00	5
125	2	2	Ring	Surface	OH	—	<b>JC002AR</b> <sup>②</sup>	22.1	7.0	3.6	390.00	5

① Dimensions shown are representative of outside box length, width, & depth and do not include allowances for mounting bumps, endwalls, covers, hubs or hardware protrusions. Dimensions are subject to change.

② Not suitable for 5th jaw applications.

③ Closure plate included.

Combination  
Meter Sockets