

# Meter Centers

## Commercial Meter Modules: Single Phase Lever Bypass



W1MM4225U

### Features

- High-quality Landis & Gyr HQ lever bypass block
- Ground lugs mounted by each position
- 225amp tenant main provisions
- Floating deadfront eliminates need for 100amp conversion kits or filler plates
- Centrally located neutral lugs
- Compact size
- 100,000 AIC Rating



W1MM2400

### Features

- High-quality Landis & Gyr HQ lever bypass block
- Factory installed 400amp tenant main breaker
- 225amp tenant main provisions
- One & Two position units now available
- 42,000 AIC Rating

3  
METERING

### 1-Phase, 3-Wire SN<sup>®</sup>, Incoming and Outgoing, Ringless Type Lever Bypass Gangable Meter Stacks

Thru-Bus Rating (amps)	Max Tenant Breaker (amps)	Meter Positions Per Stack	Catalog Number	Old Catalog Number	List Price \$	Breaker Provision	Maximum AIC <sup>③</sup>	Dimensions <sup>①</sup>			Bypass Type	KO Fig.
								Height	Width	Depth		
<i>1-Phase 4-Jaw Sockets, 1 Phase-3 Wire Thru-Bus 120/240V AC Max. -Lever Bypass</i>												
1200	225	1	W1MM1225U	DL135W4	3176.00	MP-T, MP-HT, MP-MT MPP-T, MPP-HT, MPP-MT, MPP-PT <sup>⑤</sup>	100,000	23.75	23.50	9.13	Lever	A20
		2	W1MM2225U	DL235W4	6535.00		100,000	36.75	23.50	9.13	Lever	A21
		3	W1MM3225U	DL335W4	9792.00		100,000	49.75	23.50	9.13	Lever	A22
		4	W1MM4225U	DL435W4	13174.00		100,000	62.75	23.50	9.13	Lever	A23
	400	1	W1MM1400 <sup>④</sup>	DL133W4	8901.00	JXD22B400 Factory inst.	42,000	57.00	26.00	8.66	Lever	A24
	400	2	W1MM2400	—	13547.00	JXD22B400 Factory inst.	42,000	70.38	23.00	9.69	Lever	A26

① Dimensions shown are representative of box dimensions and do not include allowances for mounting bumps, hubs or hardware protrusions.  
 ② Not for use on 3 phase-4 wire delta systems.

③ Max. AIC determined by maximum AIC of tenant breakers when used in conjunction with a meter socket. Higher overall ratings may be achieved thru approved series rating combinations.

④ Alternate trip amperages available. To order, add -amperage after catalog number (350amp becomes W1MM1400-350). List price remains the same. Contact sales office for lead time.  
 ⑤ Order filler plate ECCP3U if using standard 2" wide circuit breaker (MP-T).

Group Metering