

Meter Centers

Modular Metering: Commercial Modules—Test Block Bypass



Features

- EUSERC Compliant Test Block Bypass
- Ground lugs mounted by each position
- 225amp tenant breaker provisions (breakers not included)
- Single phase modules available with three phase thru bussing
- Horizontal breaker mounting reduces install time and effort
- Floating deadfront eliminates need for 100amp conversion kits or filler plates
- Replaces gangable BY devices

3

METERING

Thru-Bus Rating (Amps)	Maximum Tenant Breaker	Socket Continuous Duty Amps	Meter Positions Per Stack	Catalog Number	List Price \$	Breaker Provisions ^③	Max. AIC	Dimensions (inches)			Stack Phasing Phases/Socket	KO Fig.
								H	W	D		
1-Phase, 3-Wire Feed & Tenant Mains 120/240V AC Max.^{①②}												
1200	225	200	1	W1MM1225USS	1563.00	MP-T, MP-HT, MP-MT,	100,000	26.5	25.5	9.0	—	A27
1200	225	200	2	W1MM2225USS	3006.00	MPP-T, MPP-HT,	100,000	46.0	25.5	9.0	—	A28
1200	225	200	3	W1MM3225USS	4489.00	MPP-MT, MPP-PT	100,000	65.5	25.5	9.0	—	A29
3-Phase, 4-Wire Feed & 1-Phase, 3-Wire Tenant Mains 120Y/208V AC Max.^①												
1200	225	200	1	W2MM1225USS	1714.00	MP-T, MP-HT, MP-MT,	100,000	26.5	25.5	9.0	1-AB	A27
1200	225	200	2	W2MM2AB225USS	3157.00	MPP-T, MPP-HT,	100,000	46.0	25.5	9.0	1-AC, 1-BC	A28
1200	225	200	2	W2MM2BC225USS	3157.00	MPP-MT, MPP-PT	100,000	46.0	25.5	9.0	1-AC, 1-AB	A28
1200	225	200	2	W2MM2CA225USS	3157.00		100,000	46.0	25.5	9.0	1-AB, 1-BC	A28
1200	225	200	3	W2MM3225USS	4639.00		100,000	65.5	25.5	9.0	1-AB, 1-BC, 1-AC	A29
3-Phase, 4-Wire Feed & Tenant Mains 240V Max.^②												
1200	225	200	1	W3MM1225USS	1895.00	QJ, QJH2,	100,000	26.5	25.5	9.0	—	A27
1200	225	200	2	W3MM2225USS	3561.00	QJ2H, HQJ2H	100,000	46.0	25.5	9.0	—	A28
1200	225	200	3	W3MM3225USS	5271.00		100,000	65.5	25.5	9.0	—	A29

① Not rated for use with 240/120V Delta systems.

② Rated for use with 240/120V Delta systems.

③ Stacks will accept equivalent Murray circuit breakers.

④ Order part number "FIFTHJAW" for field installable fifth jaw on single phase devices.