

Temporary Power Outlet Panels

Common Catalog Number Table

Catalog Number	NEMA Type Receptacle - Breaker			Metered Type		Mounting Type				Wire Extra Circuit	Shpg. Range CU or AL	Wt. (lbs.)
	Left	Center	Right	Ring Type	Ringless Type	Surface ^①	Pedestal	Back-to-Back	Lighted			
P77US	5-20R2GFI	5-20R2GFI		Unmetered		X				X	2/Ø - #14	14
P77RTS	5-20R2GFI	5-20R2GFI			Top	X				X	2/Ø - #14	26
P77TS	5-20R2GFI	5-20R2GFI		Top		X				X	2/Ø - #14	26
P77RBS	5-20R2GFI	5-20R2GFI			Bottom	X				X	2/Ø - #14	32
P77BS	5-20R2GFI	5-20R2GFI		Bottom		X				X	2/Ø - #14	32
P57US	5-20R2GFI	6-20R		Unmetered		X				X	2/Ø - #14	14
P57RTS	6-20R	5-20R2GFI			Top	X				X	2/Ø - #14	26
P57TS	6-20R	5-20R2GFI		Top		X				X	2/Ø - #14	26
P57RBS	6-20R	5-20R2GFI			Bottom	X				X	2/Ø - #14	32
P57BS	6-20R	5-20R2GFI		Bottom		X				X	2/Ø - #14	32
P777US	5-20R2GFI	5-20R2GFI	5-20R2GFI	Unmetered		X				X	2/Ø - #14	17
P777RTS	5-20R2GFI	5-20R2GFI	5-20R2GFI		Top	X				X	2/Ø - #14	26
P777TS	5-20R2GFI	5-20R2GFI	5-20R2GFI	Top		X				X	2/Ø - #14	26
P777RBS	5-20R2GFI	5-20R2GFI	5-20R2GFI		Bottom	X				X	2/Ø - #14	32
P577BS	6-20R	5-20R2GFI	5-20R2GFI	Bottom		X				X	2/Ø - #14	32
P577TS	6-20R	5-20R2GFI	5-20R2GFI	Top		X				X	2/Ø - #14	26
P577US	6-20R	5-20R2GFI	5-20R2GFI	Unmetered		X				X	2/Ø - #14	17
P577RTS	6-20R	5-20R2GFI	5-20R2GFI		Top	X				X	2/Ø - #14	26
P577RBS	6-20R	5-20R2GFI	5-20R2GFI		Bottom	X				X	2/Ø - #14	32
P577BS	6-20R	5-20R2GFI	5-20R2GFI	Bottom		X				X	2/Ø - #14	32
P137UP	14-50R	TT30R	5-20R2GFI	Unmetered			X			X	350 kcmil - #6	40
P137RTP	14-50R	TT30R	5-20R2GFI		Top			X		X	350 kcmil - #6	48
P137US	14-50R	TT30R	5-20R2GFI	Unmetered		X				X	2/Ø - #14	17
P137RTS	14-50R	TT30R	5-20R2GFI		Top	X				X	2/Ø - #14	26
P137UPL	14-50R	TT30R	5-20R2GFI	Unmetered			X		X	X	350 kcmil - #6	45
P137RTPL	14-50R	TT30R	5-20R2GFI		Top		X		X	X	350 kcmil - #6	53
P137U2B	14-50R	TT30R	5-20R2GFI	Unmetered				X		X	350 kcmil - #6	40
P137RT2B	14-50R	TT30R	5-20R2GFI		Top					X	350 kcmil - #6	40
P137RTSL	14-50R	TT30R	5-20R2GFI		Top	X		X	X	X	2/Ø - #14	32
P137TP	14-50R	TT30R	5-20R2GFI	Top			X			X	350 kcmil - #6	49
P37US	5-20R2GFI	TT30R		Unmetered		X				X	2/Ø - #14	14
P37UP	5-20R2GFI	TT30R		Unmetered			X			X	350 kcmil - #6	34
P37RTP	TT30R	5-20R2GFI			Top			X		X	350 kcmil - #6	49
P37RTS	TT30R	5-20R2GFI			Top	X				X	2/Ø - #14	26
P37U2B	5-20R2GFI	TT30R		Unmetered				X		X	350 kcmil - #6	34
P37RT2B	TT30R	5-20R2GFI			Top			X		X	350 kcmil - #6	49
P37UPL	5-20R2GFI	TT30R		Unmetered			X		X	X	350 kcmil - #6	38
P17US	5-20R2GFI	14-50R		Unmetered		X				X	2/Ø - #14	14
P17RTP	14-50R	5-20R2GFI			Top	X				X	350 kcmil - #6	49
P3US	TT30R			Unmetered		X				X	2/Ø - #14	14
P33US	TT30R	TT30R		Unmetered		X				X	2/Ø - #14	14
P33UP	TT30R	TT30R		Unmetered			X			X	350 kcmil - #6	34
P1US	14-50R			Unmetered		X				X	2/Ø - #14	14
P337US	TT30R	TT30R	5-20R2GFI	Unmetered		X				X	2/Ø - #14	14
P337UP	TT30R	TT30R	5-20R2GFI	Unmetered			X			X	350 kcmil - #6	40

① All surface devices have a factory-included closure plate.