

Standby Power Systems

Portable Generators

Portable Generators

Portable generators are contained in a steel frame with wheels for easy relocation. The generators are powered by gasoline stored in a provided gas tank. These generators are ideal for locations where space or local codes do not allow a permanently installed standby generator. They are also great for construction site temporary power, eliminating the need for temporary power poles and utility hook ups.

Features and Ratings

- Provided with 7 receptacles
 - 12V DC, 10A
 - 120V AC, 20A Duplex
 - 120V AC, 20A Duplex GFCI
 - 120V AC, 30A Locking Type (2)
 - 120/240V AC, 30A Locking Type
 - 120/240V AC, 50A
- Full pressure lubrication
- Single point lifting
- Spin-on oil filter
- Automatic idle control
- Dimensions (in): 39 x 31 x 49
- 16 gallon fuel tank
- Low oil pressure shutdown
- Solid state voltage regulator
- GFCI protection
- Anti-vibration system
- Circuit breakers included
- Battery charge cables
- Maintenance free battery
- Full 1-1/4" tubular frame
- Wheel kit
- Electronic governor
- Tune-up kit



Catalog Number	PG015	PG017 [Ⓢ]
Rated Power	15 kW	17.5 kW
Surge	22.5 kW	26.2 kW
Rated Amps @ 60Hz 120/240, 1Ø, 1.0 pf	62.5	73.0
Engine RPM	3,600	3,600
Engine Cooling	Air	Air
Fuel Capacity (gallons)	16	16
Dimensions (inches)	39 x 31 x 49	39 x 31 x 49
Weight (lbs)	450	475



Standby and Portable Generator Maintenance Kits

Maintenance Kits

Generators require routine servicing just like any other engine. It is recommended that the oil and filters be changed once a year, or every 100 hours of use, whichever ever comes first. Maintenance kits are provided for each engine type and include an oil filter, air filter, spark plugs, and tools.



Catalog Number	Description	Usage
GENMKIT1	Oil and air filter kit	7 kW
GENMKIT2	Oil and air filter kit	10 kW
GENMKIT3	Oil and air filter kit	13, 16 kW
GENMKIT4	Oil and air filter kit	20 kW
GENMKIT5	Oil and air filter kit	25 kW
GENMKIT6	Oil and air filter kit	35, 45 kW
GENMKIT7	Oil and air filter kit	60 kW
GENMKIT8	Oil and air filter kit	70, 80, 130, 150 kW
GENMKIT9	Oil and air filter kit	100 kW
GENPAINT	Touch up paint	All devices
PORTMKIT1	Oil and air filter kit	Portable 15, 17.5 kW

[Ⓢ] The 17.5 kW portable generator is provided with a manual transfer kit. The kit includes a load center (G2020L1125CU), factory installed interlock kit (ECSBPk01), a 50A utility main, 50A generator main, a

mixture of branch circuits, a 15' power cord, and an inlet box as shown. The kit is not sold separately and is not provided on the 15 kW portable generator.