



• Revised •  
03/20/2012

# Pushbutton Units and Indicator Lights

## 30mm, Black Max Corrosion Resistant, Class 52

Selector switch complete units

### Selection and ordering data

Version	Lever type	Contact blocks	Cam <sup>Ⓞ</sup>	Order no.	List Price	Pack		
					\$	unit		
<b>Selector Switches with 2 switching positions</b>								
Short lever assembled selector switch 	Maintained operation	Short lever, non-Illuminated	1 NO	A	52SX2AABK1	1		
		Short lever, non-Illuminated	1 NC	A	52SX2AABJ1			
		Short lever, non-Illuminated	1 NO + 1 NC	A	52SX2AABA1			
	Long lever assembled selector switch 	Spring return from right operation	Long lever, non-Illuminated	1 NO	A	52SW2AABK1	1	
			Long lever, non-Illuminated	1 NC	A	52SW2AABJ1		
			Long lever, non-Illuminated	1 NO + 1 NC	A	52SW2AABA1		
		Short lever, non-Illuminated	1 NO	A	52SX2ACBK1	1		
		Short lever, non-Illuminated	1 NC	A	52SX2ACBJ1			
		Short lever, non-Illuminated	1 NO + 1 NC	A	52SX2ACBA1			
			Long lever, non-Illuminated	1 NO	A	52SW2ACBK1	1	
			Long lever, non-Illuminated	1 NC	A	52SW2ACBJ1		
			Long lever, non-Illuminated	1 NO + 1 NC	A	52SW2ACBA1		
<b>Selector Switches with 3 switching positions</b>								
	Maintained operation	Short lever, non-Illuminated	1 NO + 1 NC	C	52SX2CABA1	1		
		Short lever, non-Illuminated	2 NC + 1 NO	G	52SX2GABJ2K1			
		Short lever, non-Illuminated	2 NO + 2 NC	C	52SX2CABA2			
		Long lever, non-Illuminated	1 NO + 1 NC	C	52SW2CABA1	1		
		Long lever, non-Illuminated	2 NC + 1 NO	G	52SW2GABJ2K1			
		Long lever, non-Illuminated	2 NO + 2 NC	C	52SW2CABA2			
	Spring return from right		Short lever, non-Illuminated	1 NO + 1 NC	C	52SX2CCBA1	1	
			Short lever, non-Illuminated	2 NC + 1 NO	G	52SX2GCBJ2K1		
			Short lever, non-Illuminated	2 NO + 2 NC	C	52SX2CCBA2		
				Long lever, non-Illuminated	1 NO + 1 NC	C	52SW2CCBA1	1
				Long lever, non-Illuminated	2 NC + 1 NO	G	52SW2GCBJ2K1	
				Long lever, non-Illuminated	2 NO + 2 NC	C	52SW2CCBA2	
Spring return from left		Short lever, non-Illuminated	1 NO + 1 NC	C	52SX2CBBA1	1		
		Short lever, non-Illuminated	2 NC + 1 NO	G	52SX2GBBJ2K1			
		Short lever, non-Illuminated	2 NO + 2 NC	C	52SX2CBBA2			
			Long lever, non-Illuminated	1 NO + 1 NC	C	52SW2CBBA1	1	
			Long lever, non-Illuminated	2 NC + 1 NO	G	52SW2GBBJ2K1		
			Long lever, non-Illuminated	2 NO + 2 NC	C	52SW2CBBA2		
Spring return from right & left operation		Short lever, non-Illuminated	1 NO + 1 NC	C	52SX2CDBA1	1		
		Short lever, non-Illuminated	2 NC + 1 NO	G	52SX2GDBJ2K1			
		Short lever, non-Illuminated	2 NO + 2 NC	C	52SX2CDBA2			
			Long lever, non-Illuminated	1 NO + 1 NC	C	52SW2CDBA1	1	
			Long lever, non-Illuminated	2 NC + 1 NO	G	52SW2GDBJ2K1		
			Long lever, non-Illuminated	2 NO + 2 NC	C	52SW2CDBA2		

Technical Specifications  
on page 10/169A

Ⓞ For contact operation, see cam selection table on page 10/156.