


Load Centers

Catalog Number Logic



Lug Data

Amps	Phase	Wire Range ^①	
		Main Lug Load Centers	Main Breaker Load Centers
60	1 ϕ	14-4	
100	1 ϕ	—	3-1/0
	3 ϕ	—	8-1/0
125 (4 CKT) (6 CKT & Above)	1 ϕ	14-2/0	—
	3 ϕ	4-2/0	4-2/0
150	1 ϕ	1/0-4/0	4-250 kcmil
	3 ϕ	4-3/0	2/0-300 kcmil

Amps	Phase	Wire Range ^①	
		Main Lug Load Centers	Main Breaker Load Centers
200	1 ϕ	4-250 kcmil	4-250 kcmil
	3 ϕ	4-250 kcmil	4-250 kcmil
225	1 ϕ	4-300 kcmil	4-300 kcmil
	3 ϕ	4-300 kcmil	4-300 kcmil
400 (24 and 42 CKT)	1 ϕ	(1)3/0-500 kcmil ^② (2)3/0-250 kcmil	(1or2)3/0-250 kcmil
	3 ϕ	—	(1)3/0-500 kcmil (2)3/0-250 kcmil
400 (24 and 42 CKT)	3 ϕ	(1)3/0-500 kcmil ^② (2)3/0-250 kcmil	

① All lugs are rated for Cu or Al wire. Wire range shown is maximum allowable for bending space provided. Lug may accommodate larger wire. Refer to National Electric Code for specific wire size requirements.

② 500 kcmil must be top side entry.