

Standby Power Systems

"SR" Type Transfer Switches

Features and Ratings

- UL 1008 Listed
- 100-400A
- Outdoor NEMA Type 3R
- 1-Phase and 3-Phase
- Open Transition
- Service entrance rated option
- Compatible with "R" type controllers found in 7-60 kW generators



Catalog Number	Amp	Voltage				NEMA			Service Disconnect Included
		120/240 1Ø	120/208 3Ø	120/240 3Ø	277/480 3Ø	1	3R	12	
SR100R	100	●					●		
SR100RD	100	●					●		●
SR100C	100		●				●		
SR100J	100			●			●		
SR100I	100				●		●		
SR200R	200	●					●		
SR200RD	200	●					●		●
SR200C	200		●				●		
SR200J	200			●			●		
SR200I	200				●		●		
SR400R	400	●					●		
SR400RD	400	●					●		●
SR400C	400		●				●		
SR400J	400			●			●		

AMPS	100	100 [Ⓢ]	200	200 [Ⓢ]	400	400 [Ⓢ]	400
Voltage	120/240 1Ø 120/208 3Ø 277/480 3Ø	120/240 1Ø	120/240 1Ø 120/208 3Ø 277/480 3Ø	120/240 1Ø	120/240 1Ø 120/208 3Ø	120/240 1Ø	277/480 3Ø
Withstand Rating 1Ø 3Ø	10 kAIC 14 kAIC	10 kAIC	10 kAIC 25 kAIC	10 kAIC	18 kAIC 18 kAIC	18 kAIC	35 kAIC
Dimensions 12/240 & 120/208 277/480	24 x 20 x 7 36 x 24 x 10	24 x 13 x 7	24 x 15 x 7 48 x 30 x 12	24 x 13 x 7	36 x 24 x 10	40 x 30 x 10	48 x 30 x 12
Weight (lbs) 120/240 1Ø 120/208 3Ø 277/480 3Ø	31 49 95	39	31 49 105	40	88 107	100	105

[Ⓢ] Service entrance rated, main disconnect provided (type QP for 100A, QN for 200A).