



Pushbutton Units and Indicator Lights

30 mm Heavy Duty, Watertight/Oiltight, Class 52

• Revised •
03/20/2012

Selector switch complete units

Selection and ordering data

Version	Lever type	Contact blocks	Cam ^①	Order no.	List Price	Pack
					\$	unit
Selector Switches with 2 switching positions						
Short lever assembled selector switch	Maintained operation	Short lever, non-Illuminated	1NO	A	52SA2AABK1	1
		Short lever, non-Illuminated	1NC	A	52SA2AABJ1	
		Short lever, non-Illuminated	1NO + 1NC	A	52SA2AABA1	
		Long lever, non-Illuminated	1NO	A	52SB2AABK1	
		Long lever, non-Illuminated	1NC	A	52SB2AABJ1	
		Long lever, non-Illuminated	1NO + NC	A	52SB2AABA1	
	Spring return from right operation	Short lever, non-Illuminated	1NO	A	52SA2ACBK1	1
		Short lever, non-Illuminated	1NC	A	52SA2ACBJ1	
		Short lever, non-Illuminated	1NO + 1NC	A	52SA2ACBA1	
		Long lever, non-Illuminated	1NO	A	52SB2ACBK1	
		Long lever, non-Illuminated	1NC	A	52SB2ACBJ1	
		Long lever, non-Illuminated	1NO + 1NC	A	52SB2ACBA1	
Selector Switches with 3 switching positions						
Long lever assembled selector switch	Maintained operation	Short lever, non-Illuminated	1NO + 1NC	C	52SA2CABA1	1
		Short lever, non-Illuminated	2NC + 1NO	G	52SA2GABJ2K1	
		Short lever, non-Illuminated	2NO + 2NC	C	52SA2CABA2	
		Long lever, non-Illuminated	1NO + 1NC	C	52SB2CABA1	
		Long lever, non-Illuminated	2NC + 1NO	G	52SB2GABJ2K1	
		Long lever, non-Illuminated	2NO + 2NC	C	52SB2CABA2	
	Spring return from right	Short lever, non-Illuminated	1NO + 1NC	C	52SA2CCBA1	1
		Short lever, non-Illuminated	2NC + 1NO	G	52SA2GCBJ2K1	
		Short lever, non-Illuminated	2NO + 2NC	C	52SA2CCBA2	
		Long lever, non-Illuminated	1NO + 1NC	C	52SB2CCBA1	
		Long lever, non-Illuminated	2NC + 1NO	G	52SB2GCBJ2K1	
		Long lever, non-Illuminated	2NO + 2NC	C	52SB2CCBA2	
Spring return from left	Spring return from left	Short lever, non-Illuminated	1NO + 1NC	C	52SA2CBBA1	1
		Short lever, non-Illuminated	2NC + 1NO	G	52SA2GBBJ2K1	
		Short lever, non-Illuminated	2NO + 2NC	C	52SA2CBBA2	
		Long lever, non-Illuminated	1NO + 1NC	C	52SB2CBBA1	
		Long lever, non-Illuminated	2NC + 1NO	G	52SB2GBBJ2K1	
		Long lever, non-Illuminated	2NO + 2NC	C	52SB2CBBA2	
Spring return from right & left operation	Spring return from right & left operation	Short lever, non-Illuminated	1NO + 1NC	C	52SA2CDBA1	1
		Short lever, non-Illuminated	2NC + 1NO	G	52SA2GDBJ2K1	
		Short lever, non-Illuminated	2NO + 2NC	C	52SA2CDBA2	
		Long lever, non-Illuminated	1NO + 1NC	C	52SB2CDBA1	
		Long lever, non-Illuminated	2NC + 1NO	G	52SB2GDBJ2K1	
		Long lever, non-Illuminated	2NO + 2NC	C	52SB2CDBA2	

Technical Specifications
on page 10/169A

① For contact operation, see cam selection table on page 10/156.


• Revised •
03/20/2012

Pushbutton Units and Indicator Lights

30 mm Heavy Duty, Watertight/Oiltight, Class 52

Keyed selector switch complete units

Selection and ordering data

Version	Lever type	Contact blocks	Cam ^①	Order no.	List Price	Pack
					\$	unit
Key-operated selector switches, 2 switching positions						
Assembled keyed selector switch 	Maintained operation	Key removable in left positions	1NO	A	52SC6AFK1	1
		Key removable in left positions	1NC	A	52SC6AFJ1	
		Key removable in left positions	1NO + 1NC	A	52SC6AFA1	
		Key removable in all positions	1NO	A	52SC6AEK1	1
		Key removable in all positions	1NC	A	52SC6AEJ1	
		Key removable in all positions	1NO + 1NC	A	52SC6AEA1	
	Spring return from right operation	Key removable in left positions	1NO	A	52SC6AXK1	1
		Key removable in left positions	1NC	A	52SC6AXJ1	
		Key removable in left positions	1NO + 1NC	A	52SC6AXA1	
Key-operated selector switches, 3 switching positions						
Maintained operation	Key removable in all positions	1NC + 1NO	C	52SC6CEA1	1	
	Key removable in all positions	2NC + 1NO	G	52SC6GEJ2K1		
	Key removable in all positions	2NO + 2NC	C	52SC6CEA2		
Spring return from right operation	Key removable in all positions	1NO + 1NC	C	52SC6CZA1	1	
	Key removable in all positions	2NC + 1NO	G	52SC6GZJ2K1		
	Key removable in all positions	2NO + 2NC	C	52SC6CZA2		
Spring return from left operation	Key removable in all positions	1NO + 1NC	C	52SC6CUA1	1	
	Key removable in all positions	2NC + 1NO	G	52SC6GUJ2K1		
	Key removable in all positions	2NO + 2NC	C	52SC6CUA2		
Spring return from right & left operation	Key removable in all positions	1NO + 1NC	C	52SC6CVA1	1	
	Key removable in all positions	2NC + 1NO	G	52SC6GVJ2K1		
	Key removable in all positions	2NO + 2NC	C	52SC6CVA2		

Technical Specifications
on page 10/169A

① For contact operation, see cam selection table on page 10/156.